



NOTES:

1. 2" SIPHON NOZZLE TO BE LOCATED AFTER HYDROSTATIC TESTING AND PIGGING OF EMULSION LINE.
2. LENGTH TO BE ADJUSTED TO SUIT WALL THICKNESS. MAINTAIN 25mm CLEARANCE FROM BOTTOM OF PIPE.

0	ISSUED FOR CONSTRUCTION					
REV	REVISION	DATE:	DRN	CHK	ENG	APP
CLIENT	TITLE					
	PIPING STANDARD DETAILS LOW POINT EMULSION SIPHON					
PREPARED BY	SCALE	DWG. No.	PSD-0018	PROJ.		REV.
	N.T.S.	CLIENT				0
		DWG. No.				