



NOTES:

1. DO NOT SUPPORT, ANCHOR OR GUIDE TRACER CLOSER THAN 600 mm AT 90° CHANGE IN DIRECTION
2. STAINLESS STEEL TUBING SHALL BE HELD IN PLACE BY 304 SS BANDING 1/2"x0.015" C/W 304 SS WINGSEALS. ALL BANDING WILL BE APPLIED ON APROX. 600 mm CENTRES.
3. TOTAL EFFECTIVE LOOP LENGTH (2x"A") NOT LESS THAN 600 mm FOR 8 m RUN AND NOT LESS THAN 1 m FOR 15 m TOTAL RUN LENGTH, "B"=APPROX. 400 MIN.

0	ISSUED FOR CONSTRUCTION					
REV	REVISION	DATE	DRN	CHK	ENG	APP
CLIENT	TITLE					
	GLYCOL TRACING ANCHOR AND GUIDE DETAILS					
PREPARED BY	SCALE	DWG. No.	GT-009	PROJ.	REV.	
	N.T.S.	CLIENT DWG. No.			0	